

## SpO<sub>2</sub>-Sensoren wiederverwendbar



### SoftCap-Fingersensor

Nihon Kohden, 160 cm	SC4047
Philips, 200 cm	SC4007
Nellcor (Non OxiMax), 90 cm	SC4001



### SoftCap-Fingersensor, Kinder

Nihon Kohden, 160 cm	SCP4047
Philips, 200 cm	SCP4007
Nellcor (Non OxiMax), 90 cm	SCP4001



### SoftFlap-Fingersensor

Nihon Kohden, 160 cm	SF4047
Philips, 200 cm	SF4007
Nellcor (Non OxiMax), 90 cm	SF4001



### SoftWrap-Fingersensor

Nihon Kohden, 160 cm	W4047
Philips, 200 cm	W4007
Nellcor (Non OxiMax), 90 cm	W4001



### Klettbänder











Klettband zu SoftWrap-Fingersensor (12 Stk.)	5020621001
--	------------



### Ohrsensor

Nihon Kohden, 160 cm	EP4047
Philips, 200 cm	EP4007
Nellcor (Non OxiMax), 90 cm	EP4001

### Mögliche Sensoranschlüsse

	Nellcor	Datex			HP/Philips		BCI	Nonin	bluepoint	Nihon Kohden
Typ	4001 <sup>1</sup>	4011	4012	4013	4007	4008	4021	4026	6500	4047
Kabel- länge	90 cm	90 cm	295 cm	295 cm	200 cm	295 cm	120 cm	90 cm	90 cm	160 cm
Stecker										

1) Non OxiMax Technologie

### Verlängerungskabel



Nellcor Sensor Extensions-Kabel, 1.2 m	B-DEC-4
Nellcor Sensor Extensions-Kabel, 2.4 m	B-DEC-8